

1/4" Brass Female Open Flow Quick Disconnect • Oxygen Service

SKU: 6537K73-O2

Price: ?39.12



Description

Cleaned for oxygen service. Sockets are sleeve-lock style. To connect, slide back the sleeve on the socket, insert the plug, and release the sleeve. To disconnect, slide back the sleeve and pull out the plug. There is no valve in these sockets, so they allow for maximum flow. All open-flow sockets are compatible with any of the open-flow plugs of the same coupling size, regardless of the pipe or barb size. Brass sockets have good corrosion resistance and low wear resistance. They are softer and easier to thread than stainless steel sockets.

Maximum pressure: 5200 psi @ 72°F (359 bar @ 22°C)

Temperature range: -40° to 250°F (-40° to 121°C)

Warning: Flow should be stopped before you disconnect your line.